



prisma SOFT and prisma SMART.

Flexible Therapy for
Obstructive Sleep Apnea (OSA)



With prisma SOFT and prisma SMART discover
the new generation of our CPAP/APAP devices.

You'll make the right choice with prisma SOFT or prisma SMART! The two innovative, simple-to-use devices complete the prismaLINE spectrum.

Benefit from our two all-rounders, pragmatically designed for practical use. That goes for all our products. For we always develop with our partners' requirements in mind and create intuitively used devices that are reliable, economical and state-of-the-art.

- Unheard-of silence
- Standard operating concept and clearly structured, target group-oriented menus (for patients and experts)
- Large LCD monitor – highly visible display of information
- prismaLINE range of accessories
- Two different APAP dynamics in prisma SMART – the right therapy for every patient
- Familiar features such as recognition of Cheyne-Stokes respiration and Forced Oscillation Technology (FOT) in the entire prismaLINE

A Company of the Löwenstein Group

WEINMANN
medical technology

Accessories



prismaAQUA – WM 29680
humidifier



Ventilation mask
e.g., JOYCEone
WM 25260 (nasal)
WM 25290 (full face)



HYBERNITE Superday, Ø 22 mm – WM 29045
heated breathing tube

Accessories (optional)

not shown

DC-adapter – WM 24469

prismaTS – WM 93335

Therapy software, complete with USB data cable

Set of 12 pollen filters – WM 29652

Breathing tube, Ø 22 mm – WM 24445

Breathing tube, autoclavable, Ø 22 mm – WM 24667

prismaPSG - WM 29690

PSG module

prismaHUB - WM 31660

Communications module

Technical Data

Product class as per EU Directive 93/42/EEC	IIa	Power consumption at	230 V	115 V
Dimensions (W x H x D)	170 x 135 x 180 mm	• Operation (therapy):	0.13 A	0.22 A
Weight	about 1.34 kg	• Standby:	0.036 A	0.053 A
Temperature range	• Operation: +5 °C to +40 °C • Storage: -25 °C to +70 °C	Classification as per EN 60601-1-11		
Air pressure range	700 – 1060 hPa corresponds to an altitude of 3000 meters above mean sea level	• Type of protection from electric shock:	Protection class II	
Electrical output	max. 40 VA	• Level of protection from electric shock:	Type BF	
System interface	24 V DC max. 5 VA	• Protection from damaging ingress of water and solids:	IP21	
		Mean sound pressure level/ Operation as per ISO 80601-2-70	about 26 dB(A) at 10 hPa (corresponds to a sound pressure level of 34 dB(A))	
		Recommended maximum oxygen flow	15 liters/minute	

Other data can be found in the instructions for use.

Device description	Art. Nr.
prisma SOFT	31650-1110
prisma SMART	31620-1110

CE 0197

pdb-1000|en|1604
© Copyright protected. Copying or reproduction of any sort requires the explicit approval of Weinmann.



A Company of the Dräger Group

WEINMANN
medical technology